

Test Case	3n-hsw x1710	3n-skx xxv710	Diff
1518b-1c-ethip4ipsec4tnlsw	0.3 ± 0.0	0.7 ± 0.0	+156.1 ± 0.6
1518b-1c-ethip4ipsec10000t	0.3 ± 0.0	0.7 ± 0.0	+150.8 ± 1.0
imix-1c-ethip4ipsec4tnlsw-	0.7 ± 0.0	1.7 ± 0.0	+138.9 ± 0.6
imix-1c-ethip4ipsec1000tnl	0.7 ± 0.0	1.6 ± 0.0	+130.8 ± 0.7
imix-1c-ethip4ipsec1000tr	0.7 ± 0.0	1.5 ± 0.0	+123.5 ± 1.2
imix-1c-ethip4ipsec1000tnl	2.8 ± 0.4	5.6 ± 0.0	+97.9 ± 25.0
1518b-1c-ethip4ipsec4tnlsw	0.8 ± 0.0	1.5 ± 0.0	+94.6 ± 0.6
imix-1c-ethip4ipsec4tnlsw-	3.5 ± 0.0	6.3 ± 0.0	+81.9 ± 2.1
imix-1c-ethip4ipsec4tnlsw-	1.9 ± 0.0	3.4 ± 0.0	+81.2 ± 1.0
1518b-1c-ethip4ipsec1000t	0.7 ± 0.0	1.2 ± 0.0	+78.4 ± 1.9
imix-1c-ethip4ipsec1000tnl	1.6 ± 0.0	2.7 ± 0.0	+71.2 ± 1.3
imix-1c-ethip4ipsec4tnlsw-	1.7 ± 0.0	2.9 ± 0.0	+70.8 ± 2.4