

Test Case	3n-hsw xl710	3n-skx xxv710	Diff
1518b-1c-ethip4ipsec4tnlsw	0.3 ± 0.0	0.7 ± 0.0	+156.8 ± 1.2
1518b-1c-ethip4ipsec10000t	0.3 ± 0.0	0.7 ± 0.0	+150.4 ± 1.3
imix-1c-ethip4ipsec4tnlsw-	0.7 ± 0.0	1.7 ± 0.0	+138.0 ± 0.7
imix-1c-ethip4ipsec1000tnl	0.7 ± 0.0	1.6 ± 0.0	+132.1 ± 1.0
imix-1c-ethip4ipsec10000tr	0.7 ± 0.0	1.5 ± 0.0	+124.7 ± 1.6
1518b-1c-ethip4ipsec4tnlsw	0.8 ± 0.0	1.5 ± 0.0	+94.7 ± 1.5
imix-1c-ethip4ipsec4tnlsw-	3.5 ± 0.0	6.8 ± 0.0	+92.0 ± 0.7
imix-1c-ethip4ipsec1000tnl	3.0 ± 0.0	5.7 ± 0.0	+87.2 ± 1.8
imix-1c-ethip4ipsec4tnlsw-	1.9 ± 0.0	3.4 ± 0.0	+81.8 ± 1.1
imix-1c-ethip4ipsec4tnlsw-	1.7 ± 0.0	3.1 ± 0.0	+81.6 ± 1.1
imix-1c-ethip4ipsec1000tnl	1.5 ± 0.0	2.7 ± 0.0	+81.4 ± 1.7
1518b-1c-ethip4ipsec10000t	0.7 ± 0.0	1.2 ± 0.0	+78.3 ± 1.9